



AMMS 18-1 OPTO-COUPLER MODULE

IN: 30 VDC - OUT: 30 VDC / 1,2 A

Transistor 2 A
24 V DC

[Link to Product](#)

Illustration



Product may differ from Image

Input

Voltage range ON	6...30 V DC
Input current	8.5 mA (24 V DC)
LED display	LED (red)

General data

Test isolation voltage	2.5 kV
Housing	Black plastic, flame retardant
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+60 °C

Output

Switching voltage	6...30 V DC
Output current	max. 1.2 A
Switching time ON/OFF	1.5 µs/1 ms
Switching frequency	max. 20 kHz

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1