



RevNo	Revision note	Date	Signature	Checked
-------	---------------	------	-----------	---------



NOTES:  
 1:100% short,open and miss wire test.  
 2:Insulation resistance:DC200V 10MΩ(Min)  
 Conduction resistance 5Ω(Max)  
 3:Screws need to install in the P1 side.



⑥	SCREW	THUMB SCREW #4-40*15	2	PCS
⑤	NUT	NUT-NICKEL PLATED #4-40	2	PCS
④	OUTER MOLDED	BLACK 45P PVC	0.024	KG
③	INNER MOLDED	LDPE	0.024	KG
②	CONNECTOR	USB A/FEMALE,GOLD PLATED PIN,NICKEL PLATED SHELL,WHITE INSULATION	2	PCS
①	CABLE	UL2725 28AWG*1P+24AWG*2C+AL-FOIL+D(7/0.12BC)+BRAID(64/0.1CCS) BLACK PVC JACKET,OD;ø4.8±0.2MM	220	MM
NO.	MATERIAL	DESCRIPTIONG	QTY.	UNIT

Ltemref	Quantity	Title/Name,designation,material,dimension etc	Article No./Reference		
Designed by ACHY	Checked by HELEN	Approved by - date OCT 31.2013	File name USB AF/AF 0.135M	Date OCT 31.2013	Scale FREE
ANGLE:			ADAPTOR LEAD, USB A TO A, SOCKETS, 135MM		
UNIT:MM			AV23285(PSG03800)	Edition 1	Sheet 1/1