



12W

VT-857 12W LED GARDEN LAMP COLORCODE:GREEN BLACK BODY

Lumens <b>720</b>	Beam Angle <b>30</b>	Dimensions <b>73x255mm</b>
----------------------	-------------------------	-------------------------------

GREEN  
 SKU:7546

**2 YEARS**  
 WARRANTY



### Technical Information

Instant Start:	0-100% in
Watts:	12
Lumens:	720
On/Off Cycles:	15000
Beam Angle:	30
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours

LED Chip Type:	COB
IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.6
CRI:	>80
Operation Temperature:	-20 to +45°C
Input Power:	AC:100-240V,50/60Hz

### Features

- ✓ Perfectly designed IP65 rated garden spike with LED
- ✓ Works perfectly in extreme temperatures from -20° to +45° without any adverse etc
- ✓ Sturdily built with an Aluminium body
- ✓ Easy to Install and low maintenance
- ✓ Applications - Suitable for Gardens, Landscapes, Tree uplighting etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.46
Unit CBM	0.001224

### Listing Details

EAN Code	3800157633468
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	1000

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES