


Coaxial PCB Connector 85_MM CX-50-0-1/111_O

Description

Right angle PCB jack

Interface Standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0006 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00083972
Catalogue drawing	DCA-00012837
Mounting hole	DOU-00012639

Ordering Information

Bulk 100 pcs package	85_MM CX-50-0-1/111_OH
Single package	85_MM CX-50-0-1/111_OE

Remarks

PCB connector without stand-offs