

## Beacon 50W Mains Voltage - Hi-Spot ES50

BEACON ES50 3/C BLACK 240V  
2041884



### Product features



## PRODUCT OVERVIEW

Product name	BEACON ES50 3/C BLACK 240V
Technology	LED/Halogen
Housing	Aluminium
Mount	Track mounting
Environment	Interior
General application	Hospitality, Museums & Galleries, Retail
ETIM Class	EC001744
E-number FI	4276126
E-number SE	7416262
E-number Norway	3223670
Warranty	5 years
LOR (%)	87
Light colour	N/A
Beam Angle (°)	25
Light source included	Fixture without Lightsource
Electrical protection	Class I
Housing colour	Black
IP rating	IP20
Product EAN number	5025768418848

## DATA TABLE

### General data

Product name	BEACON ES50 3/C BLACK 240V
Technology	LED/Halogen
Housing	Aluminium
Mount	Track mounting
Environment	Interior
General application	Hospitality, Museums & Galleries, Retail
ETIM Class	EC001744
E-number FI	4276126

## Beacon 50W Mains Voltage - Hi-Spot ES50

*BEACON ES50 3/C BLACK 240V*  
2041884

E-number SE	7416262
E-number Norway	3223670
Warranty	5 years

### Optical data

LOR (%)	87
Light colour	N/A
Adjustable chromaticity	N
Beam Angle (°)	25
Distribution type	Adjustable

### Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	230V
Electrical protection	Class I
Transformer required	No

### Physical data





Housing colour	Black
IP rating	IP20
Nominal Product Width (mm)	85
Nominal Product Height (mm)	114
Nominal Product Diameter (mm)	58
Max. Lamp Diameter (mm) - D	58
Weight (kg)	0.31

### Packaging

Single packaging type	Carton
Product EAN number	5025768418848
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

## PHOTOMETRY

## Beacon 50W Mains Voltage - Hi-Spot ES50 BEACON ES50 3/C BLACK 240V 2041884



### TECHNICAL DRAWINGS

