

## Workplace mats made of PVC, oil-resistant

Diamond structure, height 10 mm

### Application:

Resistant against most chemicals and oils thanks to revolutionary PolyNit® coating. Suitable for wet and dry indoor areas.

### Version:


- Black, closed 100% PVC mat with PolyNit® coating
- Anti-slip and non-skid surface with diamond structure for sure footing
- Resistant to oils and chemicals
- With 4 all-round bevelled outside edges, even on mats cut to size
- Slip prevention R11 according to DIN 51130:2010
- Fire protection class: Conforms to BS EN ISO 11952-2:2002. Classification: Efl. Conforms to BS EN ISO 9239-1:2002. Classification: Dfl S1.

### Advantage:

- The ultimate workplace mat made of PVC for practically any environment
- Relieves the back and leg muscles and prevents premature fatigue during extended periods of standing
- Improves stepping safety on slippery workplaces

### Delivery:

Sold by the metre up to max. length 18.3 m: We will be happy to cut the desired length to size. Mats which have been cut to size cannot be returned.



<b>Art. no.</b>	<b>50225 684</b>
<b>Surface structure</b>	Diamond / closed
<b>Material</b>	PVC - Polyvinyl chloride
<b>Length</b>	1000 mm
<b>Width</b>	900 mm
<b>Material thickness</b>	10 mm
<b>Mat design</b>	Bulk stock
<b>Resistance against</b>	Oil, Acid, Fats, Petrol, Coolant
<b>Min. temperature resistance</b>	0 °C
<b>Max. temperature resistance</b>	60 °C
<b>Suitable for wet areas</b>	Yes
<b>Antistatic</b>	No
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Compliant with REACH</b>	Yes
<b>Colour</b>	Black

### EAN-Code

5013745001435