

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm



Application:

For day-to-day hard use in workshops

Version:

- All drawers with full extension
- Standard individual drawer lock to prevent tipping of the cabinet
- Perforated, slotted drawers provide a strong hold
- Very robust construction for stringent and wide-ranging requirements

Advantage:

- Optimum drawer surface height provides ideal protection against items falling out and becoming lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to crossbar-less differential extension
- Full extension - clear overview and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers Ø 100 mm



Art. no.	50301 031
Number of drawers	7 PCS
Height	990 mm
Width	564 mm
Depth	725 mm
Height x width x depth	990 x 564 x 725 mm
Housing height	800 mm
Draw width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Load-carrying capacity per drawer	75 kg
Drawer lock	Single lock right
Drawer front height	1 x 50 mm, 2 x 75 mm, 2 x 100 mm, 2 x 150 mm
Body colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Cabinet equipment	Pair of castors
With sliding handle	Yes
Height of roller carrier pair	137 mm
Wheel diameter	100 mm
Material of wheel	Nylon (polyamide)
Information about the direction	Along
Load-carrying capacity of roller	400 kg
Opening/closing system	Key Lock
Rim height	53 mm
Clear height	700 mm
LISTA unit	27 x 36 E

EAN-Code

7612269000726