



| | |
|---|---|
| <p>fitted with work equipment connected load power consumption luminous flux luminous efficacy light distribution Beam Angle light color color rendering index (CRI) system of protection class of protection technology usage luminaire body lamp cover weight (net) mains supply</p> <p>design fastening dimension special features</p> | <p>LED without 20-28V; DC approx. 10.5 W approx. 1120 lm approx. 107 lm/W direct, narrow-angled beam 40°/80° neutral white, approx. 5000 K > 80 IP 67 III switchable external aluminium, anodized, aluminium colored anodized screen, clear approx. 0.5 kg (1.1 lb) built-in plug M12 4-pole A-coded mounted version L-angle, clamp A=365 mm (14.4 in) angle of illumination 40°</p> |
|---|---|




M12 4-pole A-coded

illuminance

Comment: d=100cm

Em: 487 lx
Emax: 846 lx
Emin: 181 lx



luminous intensity

