


# 2000 Slide Switches - up to 5 position

10A 250Vac



## Key Features


- Slide switches
- Ratings up to 16A, 250V ac
- PCB and solder terminals
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators


















## Approvals and specifications

- ☑ 10A 250Vac T85  
6(3)A 250Vac T85
  - ☑ UL CSA 16A 250Vac Non Inductive  
UL CSA 4A 300Vac  
UL 65°C, file no. E45221, CSA file no. LR10990
- μ contact gap  
Please specify: Standard action (SP116) or Light action (SP118).  
2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider
<p><b>K</b></p> <p>2.8 x 0.8</p> <p><b>R</b></p> <p>2.8 x 0.8</p> <p><b>T</b></p> <p>Solder</p> <p><b>X</b></p> <p>PCB 0.8 Sq.</p> <p><b>Y</b></p> <p>PCB 0.8 Sq.</p> <p>For mounting stability switches have extra "support" terminals</p> <p>* Nominal - Dimension varies with body type. For exact figure call sales</p>	<p><b>2</b></p> <p><b>3</b></p> <p><b>4</b></p> <p><b>5</b></p>	<p><b>2</b></p> <p>Switching positions</p> <p><b>3</b></p> <p>Switching positions</p> <p><b>4</b></p> <p>Switching positions</p> <p><b>5</b></p> <p>Switching positions</p>	<p><b>10</b></p> <p><b>20</b></p> <p><b>30</b></p> <p><b>40</b></p> <p><b>10</b></p> <p><b>20</b></p> <p><b>30</b></p> <p><b>40</b></p> <p><b>10</b></p> <p><b>20</b></p> <p><b>30</b></p> <p><b>40</b></p> <p><b>10</b></p> <p><b>20</b></p> <p><b>30</b></p> <p><b>40</b></p>	<p><b>0</b></p> <p><b>1</b></p> <p><b>2</b></p> <p><b>3</b></p> <p><b>4</b></p> <p><b>5</b></p> <p><b>6</b></p> <p><b>7</b></p> <p><b>9</b></p> <p><b>A</b></p> <p><b>B</b></p> <p><b>C</b></p> <p><b>D</b></p> <p><b>E</b></p> <p><b>G</b></p> <p><b>H</b></p> <p><b>J</b></p> <p><b>K</b></p> <p><b>L</b></p> <p><b>N</b></p> <p><b>P</b></p> <p><b>R</b></p> <p><b>S</b></p> <p><b>T</b></p>

## Examples



Body		Options	Dimensions		
<p><b>C</b> 2 positions</p> 	<p><b>H</b> 2 positions</p> 	<p><b>Colour</b> Call sales for custom colours. A full range is available for large orders.</p> <p><b>Legend printing</b> A wide range is available. For all options call sales</p>	<p><b>C</b> 2 positions</p> 	<p><b>H</b> 2 positions</p> 	<p><b>Cut-out / PCB Matrix</b></p> 
<p><b>A</b> 3 positions</p> 	<p><b>H</b> 3 positions</p> 		<p><b>A</b> 3 positions</p> 	<p><b>H</b> 3 positions</p> 	<p><b>Cut-out / PCB Matrix</b></p> 
<p><b>A</b> 4 positions</p> 	<p><b>H</b> 4 positions</p> 		<p><b>A</b> 4 positions</p> 	<p><b>H</b> 4 positions</p> 	<p><b>Cut-out / PCB Matrix</b></p> 
<p><b>A</b> 5 positions</p> 			<p><b>A</b> 5 positions</p> 		<p><b>Cut-out / PCB Matrix</b></p> 