


**PDM11**

<b>Carton Box pieces</b>	<b>Qty</b>	1
<b>Product</b>		Foot Switch
<b>Model</b>		with 1mt Cable
<b>Contact</b>		1CO
<b>Color</b>		Black
<b>Current</b>	<b>Ie</b>	6 A (250V AC)
<b>Usage Category</b>		AC 15
<b>Mechanical Life</b>	<b>Min Qty</b>	1000000
<b>Electrical Life</b>	<b>Min Qty</b>	100000
<b>Operating Frequency</b>	<b>On-Off/Hour</b>	Mech. 1800 Elec. 1200
<b>Insulation Voltage</b>	<b>Ui</b>	660V
<b>Impulse Withstand Voltage</b>	<b>Uimp</b>	2.5 kV
<b>Dielectric Strength (Body-Contact)</b>		2.500V AC
<b>Dielectric Strength (Contact-Contact)</b>		1.890V AC
<b>Isolation Resistance</b>		10 MΩ min. (500V DC)
<b>Operating Temperature</b>		-25 / +80 °C
<b>Pollution Degree</b>		3
<b>Protection Degree</b>		IP20
<b>Contact Material</b>		AgNi
<b>Cable Section</b>		1.5-2.5 mm <sup>2</sup>
<b>Screw Torque</b>		1.5Nm
<b>Short Circuit Breaking Capacity</b>	<b>Ics</b>	1 kA
<b>Body Material</b>		Plastic
<b>Serial</b>		PDM Series
<b>Specifications</b>		Plastic
		Single speed
<b>Standards / Certificates</b>		TS EN 60947-5-1

CE

ERT

