


E2M204



Adapter cables for cameras with video output


CONNECTION CABLE M16 11M



Application	
Special feature	Free from silicone; Gold-plated contacts
Design	camera with video output O2M20x
Free from silicone	yes
Electrical data	
Operating voltage [V]	< 60 DC
Protection class	II
Max. current load total [A]	4
Operating conditions	
Ambient temperature [°C]	-45...85
Protection	IP 67
Mechanical data	
Weight [g]	589.5
Materials	housing: PVC; Sealing: EPDM
Material nut	PVC / PVC
Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M16, straight; Locking: PVC; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



E2M204




Adapter cables for cameras with video output

CONNECTION CABLE M16 11M

Electrical connection

Cable: 11 m, PVC, black, Ø 6 mm; 3 x 0.34 mm² / AWG 22 + 1 x 0.11 mm² / AWG 26

Connection



Electrical connection - socket

Connector: 1 x M16, straight; Locking: PVC; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm

