



2427G

**ERGO™ 45° Bent Tip Snipe Nose
Pliers with Dual-Component Handles
and Phosphate Finish**

PRODUCT DETAILS

- Two-component ERGO™ handles: thermoplastic surface on tough polypropylene provides superior grip
- Snipe nose pliers with bent tips angled at 45° developed according to the scientific ERGO™ process
- Suitable for cutting Cu, Fe and Fe+ wire
- Equipped with a return spring featuring an on/off function
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Snipe nose pliers with bent tips angled at 45° developed with PVC handles
- Tips give a good grip and improved accessibility in confined spaces
- Slim semi-circular shaped and serrated jaws
- Sharp cutting edges for cutting softer material such as copper and plastic insulated wire
- Maximum comfort with minimum effort due to ergonomic design
- Comfortable two-component handles provide excellent grip
- Angled tips give good grip and improved accessibility in confined spaces
- Self-opening handles when spring activated



Follow the Fish!



PRODUCT ATTRIBUTES

Product: 2427 G-160

<input checked="" type="checkbox"/>	46 mm	<input checked="" type="checkbox"/>	16,5 mm	<input checked="" type="checkbox"/>	8,9 mm
<input checked="" type="checkbox"/>	3 mm	<input checked="" type="checkbox"/>	2.5 mm	<input checked="" type="checkbox"/>	12 mm
<input checked="" type="checkbox"/>	3.0 mm	<input checked="" type="checkbox"/>	1.8 mm	<input checked="" type="checkbox"/>	1.6 mm
<input checked="" type="checkbox"/>	160 g				

Product: 2427 G-200

<input checked="" type="checkbox"/>	65 mm	<input checked="" type="checkbox"/>	17 mm	<input checked="" type="checkbox"/>	9,4 mm
<input checked="" type="checkbox"/>	3 mm	<input checked="" type="checkbox"/>	2.5 mm	<input checked="" type="checkbox"/>	12 mm
<input checked="" type="checkbox"/>	3.0 mm	<input checked="" type="checkbox"/>	1.8 mm	<input checked="" type="checkbox"/>	1.6 mm
<input checked="" type="checkbox"/>	170 g				

Product: 2427 G-160 IP

<input checked="" type="checkbox"/>	46 mm	<input checked="" type="checkbox"/>	16,5 mm	<input checked="" type="checkbox"/>	8,9 mm
<input checked="" type="checkbox"/>	3 mm	<input checked="" type="checkbox"/>	2.5 mm	<input checked="" type="checkbox"/>	12 mm
<input checked="" type="checkbox"/>	3.0 mm	<input checked="" type="checkbox"/>	1.8 mm	<input checked="" type="checkbox"/>	1.6 mm
<input checked="" type="checkbox"/>	160 g				

Product: 2427 G-200 IP

<input checked="" type="checkbox"/>	65 mm	<input checked="" type="checkbox"/>	17 mm	<input checked="" type="checkbox"/>	9,4 mm
<input checked="" type="checkbox"/>	3 mm	<input checked="" type="checkbox"/>	2.5 mm	<input checked="" type="checkbox"/>	12 mm
<input checked="" type="checkbox"/>	3.0 mm	<input checked="" type="checkbox"/>	1.8 mm	<input checked="" type="checkbox"/>	1.6 mm
<input checked="" type="checkbox"/>	170 g				

