


## ALUMINIUM MOBILE RACK SATA - SATA

The easy to handle Mobile Rack supports SATA I & II, data transfer rates up to 300MB/s, plug & play and hot swapping. It comes with dust protection door, cableless point to point connection, two power connectors (15/4pin), two LEDs and one front fan.



### Specifications

- Interface: SATA - SATA
- Supports SATA I and SATA II
- Supports data transfer rates up to 150 MB/S and 300 MB/s
- Ventilation: 1x front fan
- Power connectors: 1 x 4pin and 1 x 15pin SATA
- Cableless point to point connection
- Dust protection door
- Save and easy in/out sliding mechanism
- key lock
- Supports hot swapping
- Supports plug & play
- Supports SATA RAID 0,1,5
- Power on/off switch
- LED to indicate power on/off
- LED to indicate HDD access
- Material: aluminium
- Color: beige
- Product dimensions (W x H x D): 146 x 42 x 190 mm
- Product weight: 0.715 kg

### Package contents

- 1 x Mobile Rack SATA to SATA for 3.5" HDD
- 3 x Sets of Screws
- 2 x keys
- 1 x SATA cable intern 0.5m
- 1 x User Manual

