

Set-Screw Wire Connectors



Features

- Eliminates need for restripping wire each time connection is disturbed
- Solid brass sleeves in three sizes handle 18 through 12 AWG wires
- Set-screw easily and securely applies maximum compression to conductors to ensure a vibration-resistant splice
- Permits fast visual inspection of splice
- Tough, flame-retardant shell rated at 150°C (302°F)
- UL Listed to 486C and CSA Certified to C22.2

Model	Description	Catalog #
10	Set-Screw Wire Connector, Model 10 (Box of 100)	30-210
11	Set-Screw Wire Connector, Model 11 (Box of 100)	30-211
22	Set-Screw Wire Connector, Model 22 (Box of 100)	30-222
10	Set-Screw Wire Connector, Model 10 (Box of 1,000)	30-310
11	Set-Screw Wire Connector, Model 11 (Box of 1,000)	30-311
22	Set-Screw Wire Connector, Model 22 (Box of 1,000)	30-322

Dimensions

Model	A	B	C	D	E
10	1/8	5/16	1/2	19/64	45/64
11	3/16	3/8	33/64	13/32	63/64
22	1/4	1/2	11/16	13/32	1-1/64