

10W AC-DC Installation Power Supply

5V DC, 2A

multicomp PRO

**RoHS
Compliant**



Features

- Level VI
- Universal / Full range AC input
- Fixed AC mains lead (Bare Ends)
- Class II power (no earth)
- Small & Compact design

Description

This 10-12 Watt AC/DC Installation Power supplies are offered in a low profile compact enclosure with 4 mounting tabs, a fixed AC Input Cable and DC Output Cable, Single output voltage between 5V DC – 24V DC. These highly reliable power supplies can be used in many indoor applications such as CCTV, Access control and Building Management Systems.

Specifications

Voltage	5V DC
Current Max	2A
Power	10W
Line Regulation	±5%
Ripple & Noise	100mV
Protections	Over Voltage, Short Circuit, Temperature
Case Size	93.7mm (L) × 47mm (W) × 26mm (H)
Weight	240g
DC Cord	1.5m
DC Plug	Straight 2.1 C+ve
Rated Input Voltage	100V DC to 240V DC
Full Input Voltage Range	90V AC to 264V AC
Full Frequency Range	47Hz to 63Hz
Efficiency	73.36%
Input Current RMS Max	300mA
Inrush Current	115V AC = 30A Max 230V AC = 60A Max
Leakage Current	<0.25mA
Input Power (No Load)	<0.3W Max. (Level V ErP/EuP / CeC Complaint)
AC Mains Lead	1.8 Metre UK Plug
Hi-Pot	3000V AC or 4242V DC 10mA 1Min. (I.P to O.P)
Operating Temperature	0°C to 40°C
Storage Temperature	-10°C to 70°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Safety Approvals	GS & CE
EMI Standards	FCC Class B, CE & VCCI
MTBF	50K

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

