


Lumina


Lumina Sync LED 2700K

3039981



Product features

- Ambient decorative Sync LED rectangular vertical wall light with direct / indirect lighting to provide a soft lighting effect, 2700K amber white colour temperature, white aluminium body and integrated LED (non-dimmable) driver, 272 lumens, 6W, 45lm/W, 2700K, IP20, RAL 9003



PRODUCT OVERVIEW

Product name	Lumina Sync LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted
Environment	Internal
General application	Hospitality, Residential & Consumer
ETIM Class	EC002892
E-number FI	4271111
E-number SE	7502648
Warranty	3 years
Fixture luminous flux (lm)	272
Luminaire efficacy (lm/W)	45
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Total power consumption (W)	6
Electrical protection	Class II
Control gear type	LED driver constant current
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	8711971399810

DATA TABLE

General data

Product name	Lumina Sync LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted

Lumina

Lumina Sync LED 2700K

3039981

Environment	Internal
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4271111
E-number SE	7502648
Warranty	3 years

Optical data

Fixture luminous flux (lm)	272
Luminaire efficacy (lm/W)	45
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Adjustable chromaticity	N

Electrical data

Total power consumption (W)	6
Mains voltage (V)	100-240V
Electrical protection	Class II
Control gear type	LED driver constant current
Transformer required	No
Dimming method	N/A
Drive current (mA)	500
Energy Efficiency Class (A->G) of contained light source	F

Lifetime data

Lifespan L70 B50	50000
Lifespan L80 B20	35000
Lifespan L90 B10	25000

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	80
Nominal Product Width (mm)	122
Nominal Product Height (mm)	80
Weight (kg)	0.288

Packaging

Single packaging type	Carton
Product EAN number	8711971399810
Packaging single length / height (cm)	12.63
Packaging single width (cm)	8.63
Packaging single depth (cm)	9.07


Lumina

Lumina Sync LED 2700K

3039981

DUN14 (outer)	18711971399817
Units per outer package	20
Packaging outer length / height (cm)	44.9
Packaging outer width (cm)	27.4
Packaging outer depth (cm)	20.5

PHOTOMETRY



Distance [m]	Cone diameter [m]	E ₀ ' [lx]	E ₁₀ ' [lx]	E ₅₀ ' [lx]
0.5	3.15	240	72.4'	3
1.0	6.30	60	72.4'	1
1.5	9.46	27	72.4'	0
2.0	12.61	15	72.4'	0
2.5	15.76	10	72.4'	0
3.0	18.91	7	72.4'	0

Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 144.8°)

TECHNICAL DRAWINGS

