

Drill vices

Mechanical clamping system

ORION[®]

Application:

For light machining work on drill presses and pillar drills.

Execution:

- Made from grey cast iron
- Precise clamping thanks to long flat rail guide
- Clamping jaws with steps and vee blocks
- Operate by hand or by toggle lever

Delivery:

1 pc. Drill vice



Art. no.	28665 120
Brand	ORION
Manufacturer Part Number	28665120
Jaws width	124 mm
Clamping width	150 mm
Jaws height	40 mm
Jaws thickness	12 mm
Body length	300 mm
Body height	82 mm
Body width	230 mm
Max. length	420 mm
Max. flute spacing	193 mm
Min. flute spacing	175 mm
Chip flute width	13 mm
Weight	16 kg
Gross Weight	14.868 kg
Product Group	282

EAN

4039247171217