

Dumper body, with floor-level emptying option

Carrying capacity 300 kg, without wheels

Application:

For the collection and disposal of all types of bulk goods and solid materials with floor-level emptying option.

Execution:

- Robust sheet steel structure with edge reinforcement
- Tilttable trough with handle
- Base frame with fork pockets
- Easily mobile using stacker
- Oil-resistant and watertight
- Protection against accidental slipping and tipping
- Optionally box-shaped or low trough
- All dimensions without wheels

Advantage:

- With floor-level emptying option

Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 261
Volume	0.4 m ³
Length	1320 mm
Width	670 mm
Tipper edge height	485 mm
Height	840 mm
Fork pocket clearance	285 mm
Fork pocket size (W x H)	170 x 55 mm
With drain valve	No
With stacker seat tilt function	No
With perforated sheet	No
Load-carrying capacity	300 kg
Surface	Lacquered
Colour	Optional
Gross Weight	77.000 kg
Product Group	5AI