

## pneumatic sheet metal shears 9036N-1

370 W



### Application:

for high-precision cutting of all aluminium and steel sheets. ideal for straight cuts, also suitable for contour cutting.

### Execution:

- continuous speed control via a rotary knob on the handle back
- with high-performance blade for maximum cutting performance
- cold-insulating handle and cold-insulated housing
- vibration-dampened through double-bearing spindle

### Delivery:

incl. coupling connector nominal width 7.2



<b>Art. no.</b>	<b>75033 100</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	9036N-1
<b>Model</b>	9036N-1
<b>Power output</b>	370 W
<b>Air consumption</b>	104 l/min
<b>Operating pressure</b>	6.3 bar
<b>Inner hose diameter</b>	10 mm
<b>Max. cutting capacity of steel</b>	1.2 mm
<b>Max. cutting capacity in aluminium</b>	1.6 mm
<b>Cutting width</b>	4.5 mm
<b>Length</b>	255 mm
<b>Weight</b>	1 kg
<b>Max. sound-pressure-level</b>	80 dB
<b>Gross Weight</b>	1.146 kg
<b>Product Group</b>	738

### EAN

4000896209668