

Charger 24V/DC SLA

MSP-C-AH-001000






Specifications & order information

Input voltage	100-240 VAC 50-60Hz	Dimensions	105x68x39mm
Input current	700-500mA	Compatible with Arjo number	700-24201
Output voltage	24 Volt DC	Packaging	Individual, 50 pcs per pallet
Output current	1000mA	M.O.Q.	1 pcs
IP Class charger	IP40	Lead time	2 working days
Operational temperature	0°C to +40°C	Article number	MSP-C-AH-01001 for EU MSP-C-AH-01002 for UK MSP-C-AH-01003 for AUS MSP-C-AH-01004 for USA
Storage temperature	-40°C to +70°C	Certification	UL2601-1 IEC60601-1 IEC60335-2-29
Case colour	Black	Approval	CE

100% compatible

- Maxi Sky 440

Design enhancements

-  **Safer** by preventing overheating and short circuit
-  **Intelligent:** When the battery pack is charged, the charger will continue as trickle charger
-  **Stronger** material



MDR Compliance

This product complies to MDR (EU) 2017/745 (EU MDR). This product is designed to restore the function off the device without affecting the performance and safety characteristics.

You can use this datasheet as a statement to competent EU authorities.

Explore more accessories or alternatives in our web shop



Wall Mounted Charger SLA 24V/DC
MSP-C-AH-00200



Charger SLA 24V/DC
MSP-C-AH-00400



Battery Pack 24V/DC 6Ah
MSP-A-AH-00200