

SMD Resistors

Thick film 0603



FEATURES:

Small size and lightweight

Suitable for both flow and re-flow soldering

Matching with placement machines

SPECIFICATION:

Housing type	0603
Rated output	0.1 W
Resistor type	Thick film
Rated voltage	75 V
Temperature range	-55...+155 °C
Dimensions L x W x H	1.60 x 0.8 x 0.45 mm

PRODUCT RANGE:

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAJ0000T5E	0 Ω	0 %	0 ppm
RND 1550603SAF0000T5E	0 Ω	±1 %	0 ppm
RND 1550603SAF100KT5E	1 Ω	±1 %	±400 ppm/°C
RND 1550603SAF150KT5E	1.5 Ω	±1 %	±400 ppm/°C
RND 1550603SAF220KT5E	2.2 Ω	±1 %	±400 ppm/°C
RND 1550603SAF270KT5E	2.7 Ω	±1 %	±400 ppm/°C
RND 1550603SAF330KT5E	3.3 Ω	±1 %	±400 ppm/°C
RND 1550603SAF470KT5E	4.7 Ω	±1 %	±400 ppm/°C
RND 1550603SAJ047JT5E	4.7 Ω	±5 %	±400 ppm/°C
RND 1550603SAF560KT5E	5.6 Ω	±1 %	±400 ppm/°C
RND 1550603SAF680KT5E	6.8 Ω	±1 %	±400 ppm/°C
RND 1550603SAF820KT5E	8.2 Ω	±1 %	±400 ppm/°C
RND 1550603SAF100JT5E	10 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0100T5E	10 Ω	±5 %	±200 ppm/°C
RND 1550603SAF110JT5E	11 Ω	±1 %	±200 ppm/°C
RND 1550603SAF120JT5E	12 Ω	±1 %	±200 ppm/°C
RND 1550603SAF160JT5E	16 Ω	±1 %	±200 ppm/°C
RND 1550603SAF150JT5E	15 Ω	±1 %	±200 ppm/°C
RND 1550603SAF180JT5E	18 Ω	±1 %	±200 ppm/°C
RND 1550603SAF200JT5E	20 Ω	±1 %	±200 ppm/°C
RND 1550603SAF220JT5E	22 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0220T5E	22 Ω	±5 %	±200 ppm/°C
RND 1550603SAF240JT5E	24 Ω	±1 %	±200 ppm/°C
RND 1550603SAF249JT5E	24.9 Ω	±1 %	±200 ppm/°C
RND 1550603SAF270JT5E	27 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0270T5E	27 Ω	±5 %	±200 ppm/°C
RND 1550603SAF300JT5E	30 Ω	±1 %	±200 ppm/°C

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAF330JT5E	33 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0330T5E	33 Ω	±5 %	±200 ppm/°C
RND 1550603SAF360JT5E	36 Ω	±1 %	±200 ppm/°C
RND 1550603SAF390JT5E	39 Ω	±1 %	±200 ppm/°C
RND 1550603SAF430JT5E	43 Ω	±1 %	±200 ppm/°C
RND 1550603SAF470JT5E	47 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0470T5E	47 Ω	±5 %	±200 ppm/°C
RND 1550603SAF510JT5E	51 Ω	±1 %	±200 ppm/°C
RND 1550603SAF549JT5E	54.9 Ω	±1 %	±200 ppm/°C
RND 1550603SAF560JT5E	56 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0560T5E	56 Ω	±5 %	±200 ppm/°C
RND 1550603SAF620JT5E	62 Ω	±1 %	±200 ppm/°C
RND 1550603SAF680JT5E	68 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0680T5E	68 Ω	±5 %	±200 ppm/°C
RND 1550603SAF750JT5E	75 Ω	±1 %	±200 ppm/°C
RND 1550603SAF820JT5E	82 Ω	±1 %	±200 ppm/°C
RND 1550603SAF910JT5E	91 Ω	±1 %	±200 ppm/°C
RND 1550603SAF1000T5E	100 Ω	±1 %	±200 ppm/°C
RND 1550603SAJ0101T5E	100 Ω	±5 %	±200 ppm/°C
RND 1550603SAF1100T5E	110 Ω	±1 %	±100 ppm/°C
RND 1550603SAF1200T5E	120 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0121T5E	120 Ω	±5 %	±100 ppm/°C
RND 1550603SAF1300T5E	130 Ω	±1 %	±100 ppm/°C
RND 1550603SAF1500T5E	150 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0151T5E	150 Ω	±5 %	±100 ppm/°C
RND 1550603SAF1600T5E	160 Ω	±1 %	±100 ppm/°C
RND 1550603SAF1800T5E	180 Ω	±1 %	±100 ppm/°C
RND 1550603SAF2000T5E	200 Ω	±1 %	±100 ppm/°C
RND 1550603SAF2200T5E	220 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0221T5E	220 Ω	±5 %	±100 ppm/°C
RND 1550603SAF2400T5E	240 Ω	±1 %	±100 ppm/°C
RND 1550603SAF2700T5E	270 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0271T5E	270 Ω	±5 %	±100 ppm/°C
RND 1550603SAF2800T5E	280 Ω	±1 %	±100 ppm/°C
RND 1550603SAF3000T5E	300 Ω	±1 %	±100 ppm/°C
RND 1550603SAF3300T5E	330 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0331T5E	330 Ω	±5 %	±100 ppm/°C
RND 1550603SAF3600T5E	360 Ω	±1 %	±100 ppm/°C
RND 1550603SAF3900T5E	390 Ω	±1 %	±100 ppm/°C
RND 1550603SAF4300T5E	430 Ω	±1 %	±100 ppm/°C
RND 1550603SAF4530T5E	453 Ω	±1 %	±100 ppm/°C
RND 1550603SAF4700T5E	470 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0471T5E	470 Ω	±5 %	±100 ppm/°C
RND 1550603SAF4990T5E	499 Ω	±1 %	±100 ppm/°C
RND 1550603SAF5100T5E	510 Ω	±1 %	±100 ppm/°C
RND 1550603SAF5600T5E	560 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0561T5E	560 Ω	±5 %	±100 ppm/°C
RND 1550603SAF6040T5E	604 Ω	±1 %	±100 ppm/°C
RND 1550603SAF6200T5E	620 Ω	±1 %	±100 ppm/°C
RND 1550603SAF6800T5E	680 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0681T5E	680 Ω	±5 %	±100 ppm/°C
RND 1550603SAF7500T5E	750 Ω	±1 %	±100 ppm/°C
RND 1550603SAF8200T5E	820 Ω	±1 %	±100 ppm/°C
RND 1550603SAJ0821T5E	820 Ω	±5 %	±100 ppm/°C
RND 1550603SAF8660T5E	866 Ω	±1 %	±100 ppm/°C
RND 1550603SAF9100T5E	910 Ω	±1 %	±100 ppm/°C
RND 1550603SAF1001T5E	1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0102T5E	1 kΩ	±5 %	±100 ppm/°C

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAF1101T5E	1.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1131T5E	1.13 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1201T5E	1.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1301T5E	1.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1501T5E	1.5 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0152T5E	1.5 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF1581T5E	1.58 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1601T5E	1.6 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1651T5E	1.65 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1801T5E	1.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1911T5E	1.91 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2001T5E	2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2201T5E	2.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0222T5E	2.2 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF2211T5E	2.21 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2321T5E	2.32 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2401T5E	2.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2431T5E	2.43 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2491T5E	2.49 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2701T5E	2.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2801T5E	2.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3001T5E	3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3091T5E	3.09 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3161T5E	3.16 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3241T5E	3.24 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3301T5E	3.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0332T5E	3.3 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF3401T5E	3.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3571T5E	3.57 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3601T5E	3.6 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3901T5E	3.9 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3921T5E	3.92 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4121T5E	4.12 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4301T5E	4.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4701T5E	4.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0472T5E	4.7 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF4751T5E	4.75 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4871T5E	4.87 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4991T5E	4.99 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5101T5E	5.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5491T5E	5.49 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5601T5E	5.6 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5761T5E	5.76 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6201T5E	6.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6491T5E	6.49 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6801T5E	6.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6981T5E	6.98 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7501T5E	7.5 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7681T5E	7.68 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8061T5E	8.06 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8201T5E	8.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8451T5E	8.45 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8871T5E	8.87 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9101T5E	9.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9531T5E	9.53 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9761T5E	9.76 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1002T5E	10 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0103T5E	10 kΩ	±5 %	±100 ppm/°C

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAF1022T5E	10.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1072T5E	10.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1102T5E	11 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1132T5E	11.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1182T5E	11.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1203T5E	120 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1202T5E	12 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1213T5E	121 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1212T5E	12.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1242T5E	12.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1302T5E	13 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1373T5E	137 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1372T5E	13.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1502T5E	15 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0153T5E	15 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF1582T5E	15.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1602T5E	16 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1652T5E	16.5 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1742T5E	17.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1802T5E	18 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1822T5E	18.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1912T5E	19.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2002T5E	20 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2102T5E	21 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2202T5E	22 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0223T5E	22 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF2212T5E	22.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2402T5E	24 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2432T5E	24.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2552T5E	25.5 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2672T5E	26.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2702T5E	27 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2802T5E	28 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2942T5E	29.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3002T5E	30 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3092T5E	30.9 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3162T5E	31.6 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3302T5E	33 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0333T5E	33 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF3402T5E	34 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3572T5E	35.7 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3602T5E	36 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3742T5E	37.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF374JT5E	37.4 Ω	±1 %	±200 ppm/°C
RND 1550603SAF3902T5E	39 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3922T5E	39.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4022T5E	40.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4122T5E	41.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4302T5E	43 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4322T5E	43.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4702T5E	47 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0473T5E	47 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF4992T5E	49.9 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF499JT5E	49.9 Ω	±1 %	±200 ppm/°C
RND 1550603SAF5102T5E	51 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5232T5E	52.3 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5492T5E	54.9 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5602T5E	56 kΩ	±1 %	±100 ppm/°C

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAF5902T5E	59 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6042T5E	60.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF604JT5E	60.4 Ω	±1 %	±200 ppm/°C
RND 1550603SAF6202T5E	62 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6342T5E	63.4 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6802T5E	68 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6982T5E	69.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7322T5E	73.2 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7502T5E	75 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7682T5E	76.8 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8062T5E	80.6 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8202T5E	82 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9102T5E	91 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9312T5E	93.1 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1003T5E	100 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0104T5E	100 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF1023T5E	102 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1103T5E	110 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1183T5E	118 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1243T5E	124 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1303T5E	130 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1403T5E	140 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1433T5E	143 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1503T5E	150 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1583T5E	158 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1603T5E	160 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1653T5E	165 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1743T5E	174 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1803T5E	180 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1823T5E	182 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1913T5E	191 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2003T5E	200 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2203T5E	220 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2323T5E	232 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2403T5E	240 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2433T5E	243 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2673T5E	267 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF2703T5E	270 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3003T5E	300 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3013T5E	301 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3243T5E	324 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3303T5E	330 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0334T5E	330 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF3603T5E	360 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3743T5E	374 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF3903T5E	390 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4123T5E	412 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4303T5E	430 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4533T5E	453 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4703T5E	470 kΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0474T5E	470 kΩ	±5 %	±100 ppm/°C
RND 1550603SAF4753T5E	475 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF4993T5E	499 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5103T5E	510 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5603T5E	560 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF5763T5E	576 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6043T5E	604 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF6203T5E	620 kΩ	±1 %	±100 ppm/°C

Art. Nr.	Resistance	Tolerance	Temperature coefficient
RND 1550603SAF6803T5E	680 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF7503T5E	750 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF8203T5E	820 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF9103T5E	910 kΩ	±1 %	±100 ppm/°C
RND 1550603SAF1004T5E	1 MΩ	±1 %	±100 ppm/°C
RND 1550603SAJ0105T5E	1 MΩ	±5 %	±100 ppm/°C
RND 1550603SAF1204T5E	1.2 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF1504T5E	1.5 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF1804T5E	1.8 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF2004T5E	2 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF2204T5E	2.2 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF4704T5E	4.7 MΩ	±1 %	±100 ppm/°C
RND 1550603SAF1005T5E	10 MΩ	±1 %	±200 ppm/°C