

CUBE67 ACCESSORIES

System interface connector

M12

Female straight

Internal system connection
with mounting socket

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	24 V DC
Operating current	max. 4 A
Mating cycles	min. 500

General data

Protection	IP65
Mounting method	Flange, hole spacing 30 mm, bore 3.3 mm
Dimensions H × W × D	80.5×40×40 mm
Connection	Female M12, 6-pole, Han-Brid® 6-pole
Temperature range	-40...+85 °C

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1