


Produktname | *Product name*: Professionelle Stiftlampe | Professional Penlight  
 Artikelnummer | *Part Number*: 1600-0160  
 Anfragenummer | *Inquiry Number*: AN201637  
 Ersteller / Datum | *Creator / Date*: LHE / 12.10.2016

Version	Change	Date	Name
V1	2D drawing	28.12.16	LHE
V0	---	12.10.16	LHE

Leuchte / light



**Technische Daten der Leuchte / technical data of the light:**



Haupt-LED-Leuchtmittel:	3W LED	Main LED illuminant:	3W LED
Schalterfunktion:	100% / Aus	Switch function:	100% / OFF

Lichtstrom: [Lumen]	130lm	Luminous flux (light output): [Lumen]	130lm
Leuchtdauer:	ca. 3h 45min	Run time:	approx. 3h 45min
Leuchtweite:	75m	Beam distance:	75m
Maximale Lichtstärke: [Candela]	1350cd	Peak beam / luminous intensity: [Candela]	1350cd
Maximale Beleuchtungsstärke: [Lux]	1350lx (Abstand: 1m)	Peak beam illuminance: [Lux]	1350lx (Distance: 1m)
Risikogruppe (EN 62471; Bewertet nach DIN IEC/TR 62778 Anhang C.2)	2	Risk group (EN 62471; Assessed with TR 62778 Annex C.2)	2

Benötigte Zellen:	2 x AAA Micro 1.5V Batterien (Alkaline; LR03/AM4/MN2400)	Battery:	2 x AAA Micro 1.5V batteries (Alkaline; LR03/AM4/MN2400)
Schutzart des Gehäuses:	IP54	Degree of protection by the enclosure:	IP54
Gehäusematerial:	Aluminium	Housing material:	Aluminium
Betriebstemperatur:	-10°C...25°C	Operating temperature:	-10°C...25°C
Lagertemperatur:	-10°C...50°C (Nur Alkaline Batterie/Batterien) -20°C...70°C (Nur Lampe)	Storage temperature:	-10°C...50°C (Alkaline battery/batteries only) -20°C...70°C (Torch only)
Empfohlene Lagerbedingungen: (Nur Alkaline Batterie/Batterien)	Temperatur: 5..25°C Luftfeuchtigkeit: 45..75%	Recommended storage conditions: (Alkaline battery/batteries only)	Temperature: 5...25°C Rel. humidity: 45...75 %
Approbationen:	CE	Approvals:	CE
Gewicht:	33g nur die Lampe 55.5g mit 2 x Batterien (wie oben beschrieben)	Weight:	33g only the torch 55.5g with 2 x batteries (as described above)
Lieferumfang:	- 2 x Batterien (wie oben beschrieben) - Gürtelclip	Shipment:	- 2 x batteries (as described above) - Belt clip
Verpackung:	Farbige Faltschachtel	Package:	Coloured folding box