

## Product information


# 97 52 65 A

## Four-Mandrel Crimping Pliers for turned contacts



- Fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- With table for calculating the settings
- Pliers in a plastic case with foam insert
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Special quality chrome vanadium electric steel, oil-hardened

General	
Article No.	97 52 65 A
EAN	4003773071594
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	604 g
Dimensions	250 x 79 x 42 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
	
Application	turned contacts (Harting; Ilme; Phoenix; Amphenol; Walther; HTS; Contact; Weidmüller)
Capacity in square millimetres	0.14 — 6 mm <sup>2</sup>
AWG	26 — 10
Number of crimping positions	1
Max. contact diameter	7.5 mm

*technical change and errors excepted*