

## DSUB FE CR KON AWG20-24 AFS2 EINZ




Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 8278
Specification	DSUB FE CR KON AWG20-24 AFS2 EINZ
HARTING eCatalogue	<a href="https://b2b.harting.com/09670008278">https://b2b.harting.com/09670008278</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Stamped contacts

### Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 20
Wire outer diameter	≤1.52 mm
Contact resistance	≤10 mΩ
Stripping length	2.5 ... 3 mm
Performance level	2 acc. to CECC 75301-802
Mating cycles	≥250

### Material properties

Material (contacts)	Copper alloy
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	500
Net weight	0.01 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140087255
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors