



## Myriad Square IP65 Silver Reflector - White Bezel

MYRIAD SQUARE IP65 FLOOD 4K PHDIM SILREF WBEZ  
2056388



### Product features

- MYRIAD SQUARE IP65 FLOOD 4000K PHASE DIMMING SILVER REFLECTOR WHITE BEZEL



### PRODUCT OVERVIEW

Product name	MYRIAD SQUARE IP65 FLOOD 4K PHDIM SILREF WBEZ
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
E-number FI	4278601
Warranty	5 years
Fixture luminous flux (lm)	1142
Luminaire efficacy (lm/W)	114
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	48
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Dimming method	Mains: leading / trailing edge
Housing colour	Aluminium
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768563883

### DATA TABLE

#### General data

Product name	MYRIAD SQUARE IP65 FLOOD 4K PHDIM SILREF WBEZ
Technology	LED
Housing	Aluminium

## Myriad Square IP65 Silver Reflector - White Bezel

*MYRIAD SQUARE IP65 FLOOD 4K PHDIM SILREF WBEZ*  
2056388

Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4278601
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	1142
Luminaire efficacy (lm/W)	114
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	48
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	10
Mains voltage (V)	230-240V
Electrical protection	Class II
Transformer required	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

### Physical data

Housing colour	Aluminium
IP rating	IP65/20
IK rating	IK02
Nominal Product Width (mm)	72
Nominal Product Height (mm)	64
Cutout Dimensions (W x L in mm or Diameter in mm)	72
Weight (kg)	0.39
Recessed Depth (mm)	64

### Packaging



Single packaging type	Carton
-----------------------	--------

## Myriad Square IP65 Silver Reflector - White Bezel

MYRIAD SQUARE IP65 FLOOD 4K PHDIM SILREF WBEZ  
2056388

Product EAN number	5025768563883
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768563883
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY



### TECHNICAL DRAWINGS

