

Beacon LED XXL

BEACON XXL WB 4K L3 BLK

2093060



Product features

- 2093060 BEACON XXL WB 4K L3 BLK Integrated LED spotlight, black RAL 9005, compact and minimalist design, ideal for double height spaces, retail and display applications, die-cast aluminium body, passive cooling heatsink, beam angle: 67° wide beam, optics: Silicone lens for controlled beam, colour temperature: 4000K neutral white, total system power: 48W, total fixture output: 4884lm, luminaire efficacy: 102lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, non-dimmable, switched only, power factor: 0.98 electrical protection: CLASS I, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, lockable positioning using Allen key, dimen...



PRODUCT OVERVIEW

Product name	BEACON XXL WB 4K L3 BLK
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
ETIM Class	EC001744
E-number FI	4278829
Warranty	5 years
Fixture luminous flux (lm)	4884
Luminaire efficacy (lm/W)	101.75
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Beam Angle (°)	67
Photobiological Risk Group	RG1
Total power consumption (W)	48
Product Voltage (V)	240
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	N/A
Housing colour	Black
IP rating	IP20
Product EAN number	5025768930609

DATA TABLE

General data

Product name	BEACON XXL WB 4K L3 BLK
--------------	-------------------------

Beacon LED XXL

BEACON XXL WB 4K L3 BLK
2093060

Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4278829
Warranty	5 years

Optical data

Fixture luminous flux (lm)	4884
Luminaire efficacy (lm/W)	101.75
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	67
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	48
Mains voltage (V)	220-240V
Product Voltage (V)	240
Lamp power factor	0.98
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	N/A
Drive current (mA)	1200
Energy Efficiency Class (A->G) of contained light source	E

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	55500

Physical data

Housing colour	Black
IP rating	IP20
Diffuser finish	Diffuse
Reflector finish	None
Nominal Product Length (mm)	85
Nominal Product Width (mm)	168
Nominal Product Height (mm)	205
Nominal Product Diameter (mm)	113

Beacon LED XXL

BEACON XXL WB 4K L3 BLK
2093060

Weight (kg)	1.375
-------------	-------

Packaging


Single packaging type	Carton
Product EAN number	5025768930609
Packaging single length / height (cm)	25.0
Packaging single width (cm)	19.5
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768930609
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	20.0

PHOTOMETRY

0.5	0.66	E(0°) E(C0)	33.5°	17935 5211
1.0	1.32	E(0°) E(C0)	33.5°	4454 1304
1.5	1.99	E(0°) E(C0)	33.5°	1990 590
2.0	2.65	E(0°) E(C0)	33.5°	1121 328
2.5	3.31	E(0°) E(C0)	33.5°	718 209
3.0	3.97	E(0°) E(C0)	33.5°	496 145

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 67.0°)



TECHNICAL DRAWINGS

