

## Electronic 3-point quick internal micrometer set

IP67



### Application:

For measuring through-bores and blind bores (from  $\varnothing$  12.5 mm) and short centring shoulders in series production.

### Execution:

- Self-centring and self-aligning
- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

### Advantage:

- Pistol grip for quick measurements using retractable lever

### Delivery:

1 measuring element, measuring heads with setting rings, battery (1 x 3 V lithium type CR 2032)



<b>Art. no.</b>	<b>31919 510</b>
<b>Brand</b>	SYLVAC
<b>Manufacturer Part Number</b>	955.6104
<b>Min./max. length measuring range</b>	10-20 mm
<b>Measuring depth</b>	58/62 mm
<b>Error limit</b>	3 $\mu$ m
<b>Data transmission type</b>	Bluetooth/Proximity
<b>Digit increment</b>	0.001 mm
<b>IP protection class</b>	IP 67
<b>Adjusting ring diameter</b>	20 mm, 12,5 mm
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863
<b>Gross Weight</b>	2.700 kg
<b>Product Group</b>	317

### EAN

7640125028737