

ToolTower, mobile

® RasterPlan

Application:


For storing and provisioning tools and small parts. Also ideal for use as an info point for centrally displaying information and notifications for customers, visitors, departments and employees.

Version:

- sturdy frame construction with base and 4 steering rollers
- with 4 external perforated panels, 10x10 mm square perforation, grid spacing 38 mm
- with 4 steering rollers, 2 of which with locking devices according to EN 1757-3

Advantage:

- square perforations in walls enable the ToolTower to be custom-equipped as per requirements
- rapid retooling and conversion of accessories for changing workplace requirements
- mobile application possible thanks to steering rollers



Art. no.	50240 253
Width	700 mm
Depth	700 mm
Punched-hole	10 x 10 mm
Height	2175 mm
Design	Mobile
Distance between centre of hole and centre of hole	38 mm
Number of steering rollers	4
Wheel diameter	125 mm
With wheel lock	Yes
With doors	No
Lockable	No
Material	Sheet steel
Colour of frame	Anthracite grey RAL 7016
Colour of perforated panel	Light grey RAL 7035
Colour of roof	Anthracite grey RAL 7016
Surface	Plastic-coated

EAN-Code

4251142250068