

Sheet metal punches, Tristar

12.5 to 63 mm



Application:

For punching holes in sheet metal.

Execution:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

Advantage:

- The sheet does not jam in the centre thanks to the triple partition

Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



| | |
|------------------------------------------------|------------------|
| Art. no. | 53829 204 |
| Brand | ALFRA |
| Manufacturer Part Number | 01774 |
| Diameter | 20.4 mm |
| Suitable for max. sheet metal thickness | 2 mm |
| Suitable for pipe (PG) | PG 13,5 |
| Screw diameter | 9.5 mm |
| Screw length | 50 mm |
| Gross Weight | 0.090 kg |
| Product Group | 554 |

EAN

4030266 122693

