

| Interface | USB 2.0 | | | | | | | | |
|---|--|----------|------|---------------|-----|---------------|------|---------------|------|
| Power Supply | USB bus-powered: DC5V +/- 0.5V | | | | | | | | |
| Power Consumption | Suspend Current: < 500 μ A Operating Current: Max. 160mA | | | | | | | | |
| Performance | Read: up to 20MB/S Write: up to 8MB/S <i>Speed depends on used flash modules and may vary.</i> | | | | | | | | |
| Model Code / Size | <table> <thead> <tr> <th>EAN Code</th> <th>Size</th> </tr> </thead> <tbody> <tr> <td>7640111166382</td> <td>8GB</td> </tr> <tr> <td>7640111166399</td> <td>16GB</td> </tr> <tr> <td>7640111166405</td> <td>32GB</td> </tr> </tbody> </table> | EAN Code | Size | 7640111166382 | 8GB | 7640111166399 | 16GB | 7640111166405 | 32GB |
| EAN Code | Size | | | | | | | | |
| 7640111166382 | 8GB | | | | | | | | |
| 7640111166399 | 16GB | | | | | | | | |
| 7640111166405 | 32GB | | | | | | | | |
| Flash Type | MLC,TLC | | | | | | | | |
| Dimensions (LxWxH) | 53*21.5*9.6mm | | | | | | | | |
| Weight | | | | | | | | | |
| Operating Systems | <p>Without Driver:</p> <ul style="list-style-type: none"> Windows 10 Windows 8 Windows 7 Windows Vista Windows XP Windows 2003 Windows 2000 MAC OS 9, OS X and higher Linux 2.6.x | | | | | | | | |
| Environmental Conditions | <p>Device in operation: 0 °C to 70 °C</p> <p>not in operation/storage: -25 °C to 85 °C</p> | | | | | | | | |
| Service/Warranty | 2 year full warranty | | | | | | | | |
| Certifications and Standard Compliance | CE, FCC, RoHS | | | | | | | | |