

MODLINK MSDD DATA INSERT

1 × SUB-D9 fem./fem.+1 × SUB-D9 male/male+1 × RJ45+1 × USB-A

RJ45; USB (form A); SUB-D9; SUB-D9

1 × RJ45, 8-pole metal, CAT5e (female/female)

1 × USB (female/female) form A

1 × SUB-D9 (female/female)

1 × SUB-D9 (male/male)

[Link to Product](#)

Illustration



Product may differ from Image

General data

Dimensions H × W × D 88×51×45 mm

Insert 2

| | |
|--------------------------|--|
| Article number | 4000-68000-1190000 |
| Operating voltage | SUB-D: max. 125 V AC/150 V DC; RJ45: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC |
| Operating current | SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A |
| Connection cross section | SUB-D: max. 0.5 mm ² (AWG 20); PS2: max. 0.22 mm ² (AWG 24) |
| Locking of ports | SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in |
| Specification | SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz - Mbit/s); USB: 2.0/Type 2dB (max. 480 Mbit/s) |
| Mounting depth mounted | SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm; USB: approx. 80 mm; PS2: approx. 32 mm |

| | |
|----------------------|----------|
| Dimensions H x W x D | 88x51x45 |
|----------------------|----------|

| | |
|----------|-----|
| Shielded | yes |
|----------|-----|

Commercial data

| | |
|-------------------|----|
| country of origin | DE |
|-------------------|----|

| | |
|-----------------------|----------|
| customs tariff number | 85369010 |
|-----------------------|----------|

| | |
|------------------------|---|
| minimum order quantity | 1 |
|------------------------|---|