


**M12 MALE 0° B CODED SHIELDED WIREABLE SCREW TERM.**5 POLE max. 0.75mm<sup>2</sup> 6-8mm PROFIBUS

M12


Male straight

Field wireable (screw terminals)

B-coded, 5-pole, shielded

[Link to Product](#)**Illustration**

# Male



Product may differ from Image

## Technical Data

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	max. 0.75 mm <sup>2</sup>
Sealing range (cable diameter)	6...8 mm
Protection	IP67 inserted and tightened (EN 60529)
Housing	CuZn, nickel plated

## General data

Temperature range	-25...+85 °C
-------------------	--------------

## Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1