


CABLE SPECIFICATION

SPEC NO. : RG6/U CCS COAXIAL CABLE

Customer No. 24-10211

Construction Item		Unit	Construction Item
Conductors	Construction	mm	$1/1.02 \pm 0.05$
	Material	---	CCS
	Filler Material	---	---
	O. D.	mm	1.02 ± 0.05
Insulators	Material	---	Foamed PE
	Diameter	mm	4.57 ± 0.01
	Average Thickness	mm	1.77 ± 0.05
	Colour	---	White
Outer Conductors	AL-PET Foil	um	AL-P-AL
	Type	---	Braid
	Material	---	ALMG
	Coverage	%	60%
	Diameter	mm	4.80 ± 0.15
Jacket	Material	---	PVC (CM)
	Diameter	mm	6.90 ± 0.15
	Average Thickness	mm	1.00 ± 0.10
	Extrusion	---	---
	Surface	---	---
	Colour	---	White
Inking	Inking Colour	---	Black
	Inking	---	Stellar Labs RG6/U TYPE COAX 75OHM 18AWG 75degC 2250MHz E188601 (UL) CM RoHS COMPLIANT
Line	Length	ft	1000

CONFIGURATION:



GENERAL TOLERANCES
(UNLESS SPECIFIED)

LENGTH: X. ± 1
 .X ± 0.2
 .XX ± 0.10
 ANGLE: X° . $\pm 1^\circ$
 .X° $\pm 0^\circ 30'$



UNIT: mm	REV:			NAME	RG6/U CCS COAXIAL CABLE
DRAWING	XIAOSHENG/2008/10/07	S. P. NO.		DWG. NO.	
CHECK		P. O. NO.		PAGE	1/1
APPROVE		SIZE			