

Han HVE HOOD SIDE ENTRY



Part number	19 34 010 0521
Specification	Han HVE HOOD SIDE ENTRY
HARTING eCatalogue	https://b2b.harting.com/19340100521

Image is for illustration purposes only. Please refer to product description.

Version

Size	24 B
Version	Side entry
Cable entry	1x M25
Locking type	Double locking lever
Field of application	Special hoods/housings for Han Hv E [®] screw terminal

Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Page 1 / 2 | Creation date 2023-02-28 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

California Proposition 65 substances Yes

Specifications and approvals

CE	Yes
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	242.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140128255
eCl@ss	27440202 Shell for industrial connectors