

## **Product information**

## 70 06 180

## **Diagonal Cutter**

DIN ISO 5749 IEC 60900 DIN EN 60900



## • The indispensable diagonal cutter for all-round use

- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



70 06 180
4003773033813
chrome-plated
chrome-plated
insulated with multi-component grips, VDE-tested
254 g
180 x 56 x 20 mm
DIN ISO 5749 DIN EN 60900 IEC 60900
does not contain SVHC
not applicable
Ø 4.0 mm
Ø 3.0 mm
Ø 2.5 mm
yes

technical change and errors excepted







clean cutting of thin copper wires, also at the cutting edge tips