

PRODUCT-DETAILS

SAMHL25/25M

25MM GALV CORE ANTI MICRO COND 25M



General Information

Extended Product Type	SAMHL25/25M
Product ID	7TCA296030R0443
EAN	5020963801525
Catalog Description	25MM GALV CORE ANTI MICRO COND 25M
Long Description	Liquidtight, Anti-Microbial Conduit, Conduit Size - Metric 25 Millimeters / US Trade Size 3/4 Inch, Outside Diameter 26.7mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 25 Meters, White

Ordering

EAN	5020963801525
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	28.5 lb 12.925 kg
--------------------	----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Suitable for indoor splash zone areas or food processing equipment
Brand / Label	Adaptaflex
Color	White
Flexibility	High
Inside Diameter	21.0 mm
Material	Galvanised Steel Core, String Packed and Thermoplastic Jacket
Nominal Size	25 mm
Number of Batteries	0
Outside Diameter	26.4 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Anti-Microbial Conduit
Radius	110 mm
UPC	786210212982

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SAMHL25/25M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SAMHL25/25M

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

