


Part Number: 1904XXIP

Type	Size	Rating	Description
LED	M8	DC	LED Wire-ended Panel Indicator

Dimensions(mm)



Part #	Colour	Vf @ 20mA	Intensity(@10mcd)
1904X1IP	Green	2.2	20
1904X2IP	Yellow	2.1	20
1904X3IP	Red	2.0	25
1904X7IP	Blue	4.5	50
1904X8IP	Orange	2.0	30

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Luminous intensity at DC
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Voltage tolerance ±10%
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 Degree of protection IP67 when used with the supplied gasket
- 8 The plastic(polycarbonate) has limited chemical resistance
- 9 RoHS & REACH SVHC compliant