

Electronic 3-point internal micrometers set IP65

Mitutoyo

Application:

For measuring through-bores and for blind holes and short centring shoulders.

Execution:

- Titanium-coated carbide (6–12 mm)
- Titanium-coated hardened steel (12–100 mm)
- LCD display, digit size 7.5 mm
- Automatic switch-off after 20 min. Non-use
- ABS function
- HOLD function
- Preset function
- Digimatic
- IP65
- Friction coupling for consistent, repeatable measuring force

Advantage:

- suitable for present use of coolants or cutting oils

Delivery:

Includes box, adjustment wrench, SR-44 battery, setting ring



Art. no.	32017 680
Brand	MITUTOYO
Manufacturer Part Number	468-982
Min./max. length measuring range	12-25 mm
Data transmission type	DIGIMATIC
Digit increment	0.001 mm
IP protection class	IP 65
Number of measurement heads	3 PCS
Adjusting ring diameter	16 mm, 20 mm
Preset function	Yes
With ABS function	Yes
Number of rechargeable batteries/batteries	3 PCS
Battery designation	1,5 V SR44
Calibration Group	I
Gross Weight	2.609 kg
Product Group	3MA

EAN

4946368562926