

Electronic dial gauge

ID-N

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Version:

- Preset function
- Counting direction can be switched
- ABSOLUTE system for reliable measurement
- LCD digit size 6.2 mm
- Digimatic
- Hold button
- ON/OFF
- IP66

Advantage:

- Graphic display in the event that tolerance is exceeded or undershot
- Flexible installation due to switchable orientation of display



Art. no.	32019 302
Length measuring range	12.7 mm
Digit increment	0.001 mm
Min./max. measurement force	0-2.5 N
Error limit	0.003 mm
Data transmission type	DIGIMATIC
IP protection class	IP 66
Functions	ABS function, On/Off, Hold-function (AE lock), Preset function, Reversal of counting direction
Absolute function	Yes
Automatic switch-off	No
Dynamic measurement	No
Preset function	Yes
Shank diameter	8 mm
Tolerance value entry	Yes
Manual tolerance markers	No
Calibration Group	CE
Colour reading classification	No
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
Rotating housing	No
Combined indicator for figure/scale reading	No
Reversible counting direction	Yes
Digit height	6.2 mm
Design	Metric
Display	Digital
Calibration Group Description	Dial gauge
WEEE (taking back waste electrical and electronic equipment)	5

EAN-Code

4946368554204