

## META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, plastic coated



### Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

### Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

### Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



<b>Art. no.</b>	<b>50167 536</b>
<b>Brand</b>	META
<b>Manufacturer Part Number</b>	20070694
<b>Height</b>	2500 mm
<b>Length</b>	1056 mm
<b>Depth</b>	536 mm
<b>Nominal length</b>	1000 mm
<b>Nominal depth</b>	500 mm
<b>Design</b>	Shelving unit
<b>Type of assembly</b>	To insert
<b>Surface</b>	Plastic-coated
<b>Design of the frame</b>	Pre-assembled
<b>Grid dimension</b>	25 mm
<b>Number of shelves</b>	6 PCS
<b>Load-carrying capacity per shelf</b>	230 kg
<b>Load-carrying capacity per field</b>	2400 kg
<b>Number of frame</b>	2 PCS
<b>Quality label</b>	RAL-RG 6 14/ 1
<b>Made in</b>	Germany
<b>Gross Weight</b>	83.298 kg
<b>Product Group</b>	508

### EAN

40262 12 101782