

Rigid ladder with steps



Execution:

- step-strut connections made of high-strength ZARGES quality flanging
- Steps and rails made of extruded aluminium profiles
- Replaceable 2-component plastic end caps which fit securely on the rail and ensure that the ladder does not slip
- rungs feature ZARGES Safer Step Technology, 80 mm deep
- wear-resistant anodised rails
- external width: 420 mm

Art. no.	50260 623
Brand	ZARGES
Manufacturer Part Number	41362
Working height	4.4 m
Number of steps	1 x 12
Length	3.62 m
Step distance	265 mm
Weight	10.3 kg
Length stabiliser bar	0.8 m
Step depth	80 mm
Rail height	68 mm
Material	Aluminium
Max. load capacity	150 kg
With Safer Step technology	Yes
Accessibility	One-sided
Anodised	Yes
Width	420 mm
ESD-capable	No
Transport width	420 mm
Transport height	73 mm
Transport length	3610 mm
Gross Weight	10.300 kg
Product Group	5AK



EAN

4003866413621