

## Serving trolley with two metal baskets

Load capacity: 250 kg



### Execution:

- 90 mm raised edges
- Spacing between load areas: 325 mm

<b>Art. no.</b>	<b>50291 237</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM4200B
<b>Load-carrying capacity</b>	250 kg
<b>Height</b>	940 mm
<b>Length</b>	1130 mm
<b>Length x width x height</b>	1130 x 550 x 940 mm
<b>ESD-capable</b>	No
<b>Width</b>	550 mm
<b>Loading surface length</b>	935 mm
<b>Loading-surface width</b>	535 mm
<b>Surface</b>	Powder-coated
<b>Loading surface size</b>	935 x 535 mm
<b>Wheel diameter</b>	125 mm
<b>Material of wheel</b>	TPE
<b>Number of steering rollers</b>	4
<b>With wheel lock</b>	Yes
<b>Gross Weight</b>	21.500 kg
<b>Product Group</b>	5AT



### EAN

7350074800970