

Letter marking stamp sets, font height 1 to 10 mm

Standard font, with impact depth limiter, nickel-plated

ORION[®]

Application:

For labelling parts

Execution:

- With depth limit
- Standard lettering
- Exactly in the centre
- DIN 1451 typeface
- Close-spaced lettering
- Hardness at end of writing: 58-60 HRC
- Maximum strength: 1200 N/mm²
- Nickel-plated

Delivery:

In plastic box



Art. no.	56932 020
Brand	ORION
Manufacturer Part Number	56932020
Character height	2 mm
Character type provided	Letters
Number of stamps	27 PCS
Length x width x height	7 x 7 x 75 mm
Surface	Nickel plated
With depth limiter	Yes
Gross Weight	0.746 kg
Product Group	577

EAN

4039247317202