

## Aluminium platform ladder with tray

### Execution:

- Stable rectangular tube side-rails
- 80 mm deep, grooved steps
- Large trapezoidal platform (400/360x425 mm)
- 4x flanged step/side-rail connection
- Conical side-rail guide for a secure footing
- Two pre-assembled handrails for safe ascent and descent
- Step spacing: 235 mm
- Ladder inclination: 70°

### Advantage:

- Practical storage tray (350x200 mm)
- Secured against spreading with two high-strength polyester straps
- safe-cap ladder joint
- ergo-pad® grip area with clamping mechanism
- nivello® ladder shoes with patented 2-axis inclination technology



<b>Art. no.</b>	<b>59002 882</b>
<b>Brand</b>	MUNK GUENZBURGER STEIGTECHNIK
<b>Manufacturer Part Number</b>	50089
<b>Working height</b>	4.1 m
<b>Number of steps</b>	9
<b>Accessibility</b>	One-sided
<b>Width (bottom)</b>	0.75 m
<b>Max. load capacity</b>	150 kg
<b>Material</b>	Aluminium
<b>Weight</b>	17 kg
<b>Delivery</b>	Disassembled - to be assembled with tools
<b>ESD-capable</b>	No
<b>Anodised</b>	No
<b>Made in</b>	Germany
<b>Rail height</b>	0.073 m
<b>Rail height of support part</b>	0.058 m
<b>Height</b>	2.82 m
<b>With storage tray</b>	Yes
<b>Platform height</b>	2.07 m
<b>Product certification</b>	Test certificate „Type tested“ / 7KFP1725-02
<b>Stride length</b>	1.75 m
<b>Pedestal width</b>	0.75 m
<b>Step depth</b>	0.08 m
<b>Transport width</b>	0.75 m
<b>Transport length</b>	3 m
<b>Transport depth</b>	0.163 m
<b>Gross Weight</b>	17.200 kg
<b>Product Group</b>	5AP

### EAN

403140550089 1