






80-Series Cutters



TAPERED

Product code	EAN code 731415+	A mm inch	B mm inch	C mm inch	D mm inch	F mm inch	Capacity mm inch	Bevel		
8143	0051021	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.2 - 1.25 0.01 - 0.05	Micro	46	1
8144	0051045	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 1.25 0.01 - 0.05	Flush	46	1
8145	0051052	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 1.0 0.01 - 0.04	Ultra	46	1
8153	0051205	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.3 - 1.6 0.01 - 0.06	Micro	49	1
8154	0052103	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.2 - 1.6 0.01 - 0.06	Flush	49	1
8155	0052110	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.2 0.05	0.2 - 1.25 0.01 - 0.05	Ultra	49	1
8163	0051342	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.4 - 2.0 0.02 - 0.08	Micro	88	1
8164	0052141	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.3 - 2.0 0.01 - 0.08	Flush	88	1
8165	0052158	125.0 4.92	16.0 0.63	16.0 0.63	8.0 0.31	1.6 0.06	0.3 - 1.6 0.01 - 0.06	Ultra	88	1

8143-8165



TAPERED AND RELIEVED

Product code	EAN code 731415+	A mm inch	B mm inch	C mm inch	D mm inch	F mm inch	Capacity mm inch	Bevel		
8146	0051076	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.2 - 1.0 0.01 - 0.04	Micro	46	1
8147	0051083	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 1.0 0.01 - 0.04	Flush	46	1
8148	0051090	110.0 4.33	10.0 0.39	10.0 0.39	6.0 0.24	0.8 0.03	0.1 - 0.8 0.01 - 0.03	Ultra	45	1
8156	0051212	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.0 0.04	0.3 - 1.25 0.01 - 0.05	Micro	49	1
8157	0052127	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.0 0.04	0.2 - 1.25 0.01 - 0.05	Flush	49	1
8158	0052134	112.5 4.43	12.5 0.50	12.5 0.50	6.0 0.24	1.0 0.04	0.2 - 1.0 0.01 - 0.04	Ultra	49	1

8146-8158

