

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

VARIOFACE Front Connect, IDC/FLK termination board for the system cabling with Push-in front connections for 8 channels and additional positive and negative potential terminal blocks for 3-conductor initiator connection, number of positions: 14, overall width: 19 mm



Your advantages

- Fast, clear, and error-free wiring, thanks to Push-in terminal blocks with front connection technology
- Up to 60 % less space required in the control cabinet compared to conventional solutions due to the innovative design with an installation width of 19 mm
- Plug and Play connection to the remote IO and field level with the comprehensive system cabling range from Phoenix Contact
- Optimum support for your distributed I/O devices, thanks to high flexibility and the slim design
- Optically and haptically compatible with modern remote IO systems

Commercial Data

Item number	1278798
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	CK2162
Product Key	CK2162
GTIN	4063151475550
Weight per Piece (including packing)	96 g
Weight per Piece (excluding packing)	96 g
Customs tariff number	85366990
Country of origin	DE

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Technical Data

Product properties

Product type	Controller board
Number of positions	14
No. of channels	8

Insulation characteristics

Overvoltage category	II
Pollution degree	2
Insulation	Functional insulation

Electrical properties

No. of channels	8
Max. permissible operating voltage	30 V AC
	60 V DC
Max. permissible current	1 A (per branch)
Rated insulation voltage	63 V
Rated surge voltage	0.8 kV (1.2/50 µs)

Supported controller SIEMENS S7-1500

Suitable I/O card	6ES7521-1BH00-0AB0
	6ES7521-1BH10-0AA0
	6ES7521-1BH50-0AA0
	6ES7521-1BL00-0AB0
	6ES7521-1BL10-0AA0
	6ES7522-1BH00-0AB0
	6ES7522-1BH01-0AB0
	6ES7522-1BL00-0AB0
	6ES7522-1BL01-0AB0
	6ES7522-1BL10-0AA0
	6ES7523-1BL00-0AA0

Supported controller ALLEN-BRADLEY ControlLogix

Suitable I/O card	1756-IB32
	1756-OB32
	1756-IN16
	1756-IB16
	1756-IC16
	1756-OB16E

Supported controller ALLEN-BRADLEY PLC 5

Suitable I/O card	1771 IBN
	1771 OBN

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Supported controller ALLEN-BRADLEY SLC 500

Suitable I/O card	1746 OB 32
	1746 OV 32
	1746 IB 32
	1746 IV 32

Supported controller GE-FANUC RX3i

Suitable I/O card	IC694MDL754
	IC694MDL660

Supported controller HONEYWELL Experion PKS C200

Suitable I/O card	TC-IDD 321
	TC-ODD 321

Supported controller MITSUBISHI MELSEC Q

Suitable I/O card	QX81
	QY81P
	QX41
	QX41-S1
	QX42
	QX42-S1
	QX71
	QX72
	QY41P
	QY42P
	QY71
	QH42P
	QX82
	QX82-S1
	QY82P

Supported controller MITSUBISHI MELSEC L

Suitable I/O card	LX41C4
	LX42C4
	LY41NT1P
	LY42NT1P
	LY41PT1P
	LY42PT1P

Supported controller SCHNEIDER ELECTRIC Modicon TSX QUANTUM

Suitable I/O card	DDI 353
	DDI 853
	DAI 453
	DDO 353

Supported controller SIEMENS ET 200SP

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Suitable I/O module	6ES7131-6BH01-0BA0 (Base Units A0/A1)
	6ES7131-6BH01-2BA0 (Base Units A0/A1)
	6ES7132-6BH01-0BA0 (Base Units A0/A1)
	6ES7132-6BH01-2BA0 (Base Units A0/A1)

Connection data

Controller level

Connection in acc. with standard	IEC 60603-13 DIN 41651
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	14

Controller level

Connection method	Push-in connection
Stripping length	10 mm
Number of positions	28
Conductor cross section solid	0.2 mm² ... 1.5 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
	0.25 mm² ... 1.5 mm² (Ferrules without plastic sleeve)
	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 16

LED signaling

Status display	No
Status display present	No

Dimensions

Width	18.9 mm
Height	127 mm
Depth	40.25 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C
Altitude	≤ 3000 m

Approval data

UL, USA / Canada

Identification	UL 61010-2-201
----------------	----------------

UL, USA / Canada

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Identification	CSA C22.2 NO. 61010-2-201
----------------	---------------------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Interface module - VFC-PT/FLK14/PLC




1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Drawings

Circuit diagram



Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Approvals



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705

cULus Listed

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Classifications

ECLASS

ECLASS-9.0	27141152
ECLASS-10.0.1	27141152
ECLASS-11.0	27141152

ETIM

ETIM 8.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Accessories

Front adapters

Front adapters - FLKM 20-PA-ET200SP - 1099751

<https://www.phoenixcontact.com/gb/products/1099751>




VARIOFACE front adapter for Siemens SIMATIC® ET200SP, with a 20-pos. FLK-/IDC male strip, max. 16 channels can be connected

Cable

Cable - FLK EZ-DR.../.../... - 2295059

<https://www.phoenixcontact.com/gb/products/2295059>



Round cable, with preassembly, not shielded, variable cable length

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK EZ-DR-S.../.../... - 2295046

<https://www.phoenixcontact.com/gb/products/2295046>

Round cable, with preassembly, shielded, variable cable length



Marker strip

Marker strip - SK 2,8 WH:REEL - 0805205

<https://www.phoenixcontact.com/gb/products/0805205>



Marker strip, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 90000 mm, lettering field size: continuous x 2.8 mm, Number of individual labels: 480000

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 30/KONFEK - 2295729

<https://www.phoenixcontact.com/gb/products/2295729>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.3 m

Cable

Cable - FLK 14/EZ-DR/ 50/KONFEK - 2288901

<https://www.phoenixcontact.com/gb/products/2288901>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 100/KONFEK - 2288914

<https://www.phoenixcontact.com/gb/products/2288914>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1 m

Cable

Cable - FLK 14/EZ-DR/ 150/KONFEK - 2288927

<https://www.phoenixcontact.com/gb/products/2288927>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 200/KONFEK - 2288930

<https://www.phoenixcontact.com/gb/products/2288930>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2 m

Cable

Cable - FLK 14/EZ-DR/ 250/KONFEK - 2288943

<https://www.phoenixcontact.com/gb/products/2288943>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 300/KONFEK - 2288956

<https://www.phoenixcontact.com/gb/products/2288956>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 3 m

Cable

Cable - FLK 14/EZ-DR/ 350/KONFEK - 2288969

<https://www.phoenixcontact.com/gb/products/2288969>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 3.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 400/KONFEK - 2288972

<https://www.phoenixcontact.com/gb/products/2288972>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Cable

Cable - FLK 14/EZ-DR/ 500/KONFEK - 2290834

<https://www.phoenixcontact.com/gb/products/2290834>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 600/KONFEK - 2290863

<https://www.phoenixcontact.com/gb/products/2290863>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 6 m

Cable

Cable - FLK 14/EZ-DR/ 800/KONFEK - 2299563

<https://www.phoenixcontact.com/gb/products/2299563>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 8 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/1000/KONFEK - 2299576

<https://www.phoenixcontact.com/gb/products/2299576>



Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 10 m

Cable

Cable - FLK 14/EZ-DR/HF/ 50/KONFEK - 2305952

<https://www.phoenixcontact.com/gb/products/2305952>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/HF/ 100/KONFEK - 2305965

<https://www.phoenixcontact.com/gb/products/2305965>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1 m

Cable

Cable - FLK 14/EZ-DR/HF/ 150/KONFEK - 2305978

<https://www.phoenixcontact.com/gb/products/2305978>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/HF/ 200/KONFEK - 2305981

<https://www.phoenixcontact.com/gb/products/2305981>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2 m

Cable

Cable - FLK 14/EZ-DR/HF/ 250/KONFEK - 2305994

<https://www.phoenixcontact.com/gb/products/2305994>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/HF/ 300/KONFEK - 2304759

<https://www.phoenixcontact.com/gb/products/2304759>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 3 m

Cable

Cable - FLK 14/EZ-DR/HF/ 400/KONFEK - 2304762

<https://www.phoenixcontact.com/gb/products/2304762>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/HF/ 500/KONFEK - 2304717

<https://www.phoenixcontact.com/gb/products/2304717>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 5 m

Cable

Cable - FLK 14/EZ-DR/HF/ 600/KONFEK - 2306003

<https://www.phoenixcontact.com/gb/products/2306003>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 6 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14-EZ-DR-HF/... - 2314040

<https://www.phoenixcontact.com/gb/products/2314040>



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: variable

Cable

Cable - FLK 14/EZ-DR/ 50/KONFEK/S - 2296977

<https://www.phoenixcontact.com/gb/products/2296977>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 0.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 100/KONFEK/S - 2296980

<https://www.phoenixcontact.com/gb/products/2296980>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 1 m

Cable

Cable - FLK 14/EZ-DR/ 120/KONFEK/S - 2299071

<https://www.phoenixcontact.com/gb/products/2299071>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 1.2 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 150/KONFEK/S - 2296993

<https://www.phoenixcontact.com/gb/products/2296993>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 1.5 m

Cable

Cable - FLK 14/EZ-DR/ 180/KONFEK/S - 2299084

<https://www.phoenixcontact.com/gb/products/2299084>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 1.8 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 200/KONFEK/S - 2297002

<https://www.phoenixcontact.com/gb/products/2297002>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 2 m

Cable

Cable - FLK 14/EZ-DR/ 300/KONFEK/S - 2299013

<https://www.phoenixcontact.com/gb/products/2299013>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 3 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 400/KONFEK/S - 2299026

<https://www.phoenixcontact.com/gb/products/2299026>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 4 m

Cable

Cable - FLK 14/EZ-DR/ 600/KONFEK/S - 2299039

<https://www.phoenixcontact.com/gb/products/2299039>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 6 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 14/EZ-DR/ 800/KONFEK/S - 2299042

<https://www.phoenixcontact.com/gb/products/2299042>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 8 m

Cable

Cable - FLK 14/EZ-DR/1000/KONFEK/S - 2299055

<https://www.phoenixcontact.com/gb/products/2299055>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position) (The braided shield is routed to a separate cable end.); cable length: 10 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50/4X14/EZ-DR/ 50/KONFEK - 2296689

<https://www.phoenixcontact.com/gb/products/2296689>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 0.5 m

Cable

Cable - FLK 50/4X14/EZ-DR/ 100/KONFEK - 2296692

<https://www.phoenixcontact.com/gb/products/2296692>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 1 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50/4X14/EZ-DR/ 150/KONFEK - 2296702

<https://www.phoenixcontact.com/gb/products/2296702>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 1.5 m

Cable

Cable - FLK 50/4X14/EZ-DR/ 200/KONFEK - 2296715

<https://www.phoenixcontact.com/gb/products/2296715>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 2 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50/4X14/EZ-DR/ 250/KONFEK - 2305402

<https://www.phoenixcontact.com/gb/products/2305402>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 2.5 m

Cable

Cable - FLK 50/4X14/EZ-DR/ 300/KONFEK - 2296728

<https://www.phoenixcontact.com/gb/products/2296728>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 3 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50/4X14/EZ-DR/ 400/KONFEK - 2296731

<https://www.phoenixcontact.com/gb/products/2296731>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 4 m

Cable

Cable - FLK 50/4X14/EZ-DR/ 600/KONFEK - 2296744

<https://www.phoenixcontact.com/gb/products/2296744>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 6 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50/4X14/EZ-DR/1000/KONFEK - 2296773

<https://www.phoenixcontact.com/gb/products/2296773>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 10 m

Cable

Cable - FLK 50-4X14-EZ-DR ... - 2302405

<https://www.phoenixcontact.com/gb/products/2302405>



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: variable

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 50-4X14-EZ-DR-S ... - 2302447

<https://www.phoenixcontact.com/gb/products/2302447>



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (4x 14-position) (The braided shield is routed to four separate cable ends.); cable length: variable

Cable

Cable - FLK 20/2FLK14/EZ-DR/ 50/KONFEK - 2305059

<https://www.phoenixcontact.com/gb/products/2305059>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 0.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 20/2FLK14/EZ-DR/100/KONFEK - 2298470

<https://www.phoenixcontact.com/gb/products/2298470>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 1 m

Cable

Cable - FLK 20/2FLK14/EZ-DR/10M/KONFEK - 2902708

<https://www.phoenixcontact.com/gb/products/2902708>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 10 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 20/2FLK14/EZ-DR/200/KONFEK - 2298438

<https://www.phoenixcontact.com/gb/products/2298438>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 2 m

Cable

Cable - FLK 20/2FLK14/EZ-DR/300/KONFEK - 2300818

<https://www.phoenixcontact.com/gb/products/2300818>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 3 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 20/2FLK14/EZ-DR/400/KONFEK - 2305237

<https://www.phoenixcontact.com/gb/products/2305237>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 4 m

Cable

Cable - FLK 20/2FLK14/EZ-DR/500/KONFEK - 2902707

<https://www.phoenixcontact.com/gb/products/2902707>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - FLK 20/2FLK14/EZ-DR/... - 2304487

<https://www.phoenixcontact.com/gb/products/2304487>



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: variable

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/0,5M - 1369888

<https://www.phoenixcontact.com/gb/products/1369888>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/1,0M - 1369897

<https://www.phoenixcontact.com/gb/products/1369897>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1 m

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/1,5M - 1369902

<https://www.phoenixcontact.com/gb/products/1369902>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1.5 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/2,0M - 1369904

<https://www.phoenixcontact.com/gb/products/1369904>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2 m

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/3,0M - 1369905

<https://www.phoenixcontact.com/gb/products/1369905>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 3 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/4,0M - 1369906

<https://www.phoenixcontact.com/gb/products/1369906>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Round cable

Round cable - CABLE-FLK14/AXIO/OE/0,14/6,0M - 1369909

<https://www.phoenixcontact.com/gb/products/1369909>



Round cable set; controller: Axioline Realtime I/O; connection 1: Single wires (8-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 6 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/ 50 - 2305761

<https://www.phoenixcontact.com/gb/products/2305761>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.5 m

Cable

Cable - CABLE-FLK14/OE/0,14/ 100 - 2305253

<https://www.phoenixcontact.com/gb/products/2305253>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/ 150 - 2305266

<https://www.phoenixcontact.com/gb/products/2305266>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1.5 m

Cable

Cable - CABLE-FLK14/OE/0,14/ 200 - 2305279

<https://www.phoenixcontact.com/gb/products/2305279>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/ 250 - 2305282

<https://www.phoenixcontact.com/gb/products/2305282>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2.5 m

Cable

Cable - CABLE-FLK14/OE/0,14/ 300 - 2305295

<https://www.phoenixcontact.com/gb/products/2305295>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 3 m

Interface module - VFC-PT/FLK14/PLC

1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/ 400 - 2305774

<https://www.phoenixcontact.com/gb/products/2305774>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Cable

Cable - CABLE-FLK14/OE/0,14/ 600 - 2305787

<https://www.phoenixcontact.com/gb/products/2305787>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 6 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/ 800 - 2305790

<https://www.phoenixcontact.com/gb/products/2305790>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 8 m

Cable

Cable - CABLE-FLK14/OE/0,14/1000 - 2305800

<https://www.phoenixcontact.com/gb/products/2305800>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 10 m

Interface module - VFC-PT/FLK14/PLC



1278798

<https://www.phoenixcontact.com/gb/products/1278798>

Cable

Cable - CABLE-FLK14/OE/0,14/... - 2305732

<https://www.phoenixcontact.com/gb/products/2305732>



Round cable set; connection 1: Single wires (14-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 14-position); cable length: variable

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk