


Synergy 21 LED LoRa (433MHz) Poolleuchte 15W RGB+CCT *Milight/Miboxer*



kwh/1000h:	16,50
Lumen:	1100
Watt:	15,0
Nennlebensdauer:	35000 Std.
Schaltzyklen:	50000
Opt. Umgebungstemp.:	25 °C





Product Name: 15W RGB+CCT Wall-mounted Underwater Light (LoRa 433MHz)
Model No.: UW01
Power: 15W
Input Voltage: AC12V / DC12~24V
Working Temperature: -20~45°
RF: 433MHz
Modulation Method: LoRa spread spectrum
Control distance: 50m (Lamps into 0.5m underwater)
Color temperature: 2700K~6500K
Luminous Flux: 1100LM
Light Efficiency: 72LM/W
CRI: >80
Lifespan: 50000h
Beam Angle: 160°
IP Rate: IP68
Housing Material: 316 Stainless Steel+PC



Energieeffizienzklasse: A
kWh/1000h: 16,5

Merkmale

Merkmal	Wert
Abstrahlwinkel:	160
CC oder CV:	CV
Dimmbar:	Ja
Grösse:	220*50
LED - Gehäusematerial:	Stahl
Lichtfarbe:	RGB-WW
Lichtfarbe in Kelvin:	2700~6500
Lumen:	1100
Schutzklasse:	IP68
Volt:	12/24
Gewicht:	1 Kg


Weitere Bilder







COMPATIBLE REMOTE SHEET



Zubehör

Art.-Nr.	Name
178057	Synergy 21 LED LoRa (433MHZ) Poolleuchte 15W RGB+CCT *Milight/Miboxer*
178058	Synergy 21 LED LoRa (433MHZ) Controller DMX über LoRa *Milight/Miboxer*
178059	Synergy 21 LED LoRa (433MHZ) Poolleuchte 27W RGB+CCT *Milight/Miboxer*
178060	Synergy 21 LED LoRa (433MHZ) Unterwasserleuchte 9W RGB+CCT *Milight/Miboxer*
178061	Synergy 21 LED LoRa (433MHZ) PAR56 Pool Light 27W RGB+CCT *Milight/Miboxer*
178062	Synergy 21 LED LoRa (433MHZ) Fernbedienung* Milight/Miboxer*

Art.-Nr.	Name
178154	Synergy 21 LED LoRa (433MHZ) Garten Lampe 25W RGB-WW mit Funk IP66 230V *Milight/Miboxer*