

PRODUCT-DETAILS

# ADR21

## AL CONN 2/0-14 AWG



### General Information

Extended Product Type	ADR21
Product ID	7TAH006600R0199
EAN	5415022348392
Catalog Description	AL CONN 2/0-14 AWG
Long Description	Type ADR-ALCUL Single-Conductor, One-Hole Mount, Conductor Range 14 AWG-2/0 Str, Length 1-15/32 Inches, Width 5/8 Inch, Height 25/32 Inch, 1/4 Inch Bolt Hole, Slotted Screw, Tin Plated

### Ordering

EAN	5415022348392
UPC	783786610082
Country of Origin	Mexico (MX)
Selling Unit of Measure	each

### Container Information

Package Level 1 Units	25 piece
Package Level 1 Width	3.125 in 79 mm
Package Level 1 Height	2.938 in 75 mm
Package Level 1 Depth /	4.25 in

Length	108 mm
Package Level 2 Units	250 piece
Package Level 2 Width	6.6 in 168 mm
Package Level 2 Height	4.7 in 119 mm
Package Level 2 Depth / Length	14.8 in 376 mm

---

### Additional Information

Brand / Label	Blackburn
Effective Date	19991027
Insulation Material	None
Material	Aluminum
Number of Conductors	1
Product Name	BLACKBURN MECHANICAL
Product Type	Dual-Rated Mechanical Connector
Spacing	1/4 in
Special Functions	Easy Installation - no special tools required.
Standards	UL E9809
Surface Finishing	Tin Plated

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	ADR21
Instructions and Manuals	ADR21

---

### Classifications

UNSPSC	39121408
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4541 >> Mechanical connectors

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

