



JD SERIES


KEY SWITCH
Ø19.2 mm PANEL CUTOUT



DESCRIPTION:

- ZINC ALLOY NICKEL-PLATED HOUSING AND 4-DISC TUMBLER CYLINDER.
- TWO SINGLE-BITTED BRASS KEYS.
- NUT OR CLIP (PLEASE SPECIFY)
- 4 AMPS 125V AC OR 28V DC, 2AMPS 250V AC

PATENT NO. 4222



LOCK CONFIGURAION (AS VIEWED FROM KEY END)	MODEL / NO. NO. / POLES	CONNECTED TERMINALS					KEY REMOVABLE IN POS.
		POS.1	POS.2	POS.3	POS.4	POS.5	
 45° INDEXING MOMENTARY	JD10B126W	8-1 4-5	1-2 5-6				POS.1
 45° INDEXING MOMENTARY	JD10F126W	8-1 4-5	1-2 5-6	7-8 3-4			POS.1

ATTACHED WIRE SPEC

TERMINAL	LENGTH(mm)	SPEC		
1	250	UL1007	20AWG	BLACK
2	250	UL1007	20AWG	BLUE
3	250	UL1007	20AWG	BROWN
4	250	UL1007	20AWG	GREEN
5	250	UL1007	20AWG	GREY
6	250	UL1007	20AWG	RED
7	250	UL1007	20AWG	VIOLET
8	250	UL1007	20AWG	YELLOW

APEM COMPONENTS LTD

Drakes Drive, Long Crendon, Bucks HP18 9BA

Tel: +44 (0) 1844 202400

Fax: +44 (0) 1844 202500

Web site: <http://www.apem.co.uk>

e-mail: sales@apem.co.uk